




AMBERLITE™ IRN217 Li/OH Ion Exchange Resin

Mixture of Nuclear-grade, Uniform Particle Size, Gel, Strong Acid Cation and Strong Base Anion Exchange Resins for Water Treatment Applications in the Nuclear Power Industry

Description

AMBERLITE™ IRN217 Li/OH Ion Exchange Resin is designed specifically for use in nuclear loops where highest resin purity and stability are required, and where the "as supplied" resin must have a minimum of ionic and non-ionic contamination. These high standards of resin purity enable plants to achieve reliable and safe production whilst reducing the need for equipment maintenance and minimizing the impact of unscheduled outages.



AMBERLITE IRN217 Li/OH is composed of AMBERLITE™ IRN77 H Ion Exchange Resin converted to the ⁷Li form at ≥ 99.9% isotopic purity and AMBERLITE™ IRN78 OH Ion Exchange Resin, supplied together on a 1:1 equivalent basis.

AMBERLITE IRN217 Li/OH is designed to be used in primary water chemistry control in PWR nuclear power operation. The resin combines the properties of high capacity and excellent physical strength. Pre-mixed resin also allows for faster change-out and initial rinse-up prior to service, which minimizes start-up time and rinse wastewater volume.

Applications

- Primary water treatment:
 - Primary coolant purification

Purity

AMBERLITE™ IRN Ion Exchange Resins are manufactured as nuclear-grade using specific procedures throughout the manufacturing process to keep the inorganic impurities at the lowest possible level. Special treatment procedures are also utilized to remove traces of soluble organic compounds to meet the rigorous demands of the nuclear industry. These high standards of resin purity will help keep nuclear systems free of contaminants and deposits, and prevent increases in radioactivity levels due to activation of impurities in the reactor core. IRN resins are recommended in both non-regenerable and regenerable single bed or mixed bed applications where reliable production of the highest quality water is required and where the "as supplied" resin must have an absolute minimum of ionic and non-ionic contamination.

Historical Reference

AMBERLITE™ IRN217 Li/OH Ion Exchange Resin has previously been sold as AMBERLITE™ IRN217 Ion Exchange Resin.

Typical Physical and Chemical Properties**

	AMBERLITE™ IRN77 H (→ ⁷ Li) Cation Resin	AMBERLITE™ IRN78 OH Anion Resin
Physical Properties		
Copolymer	Styrene-divinylbenzene	Styrene-divinylbenzene
Matrix	Gel	Gel
Type	Strong acid cation	Strong base anion
Functional Group	Sulfonic acid	Trimethylammonium
Physical Form	Amber, translucent, spherical beads	Amber, translucent, spherical beads
Ionic Ratio		
	1:1	1:1
Chemical Properties		
Ionic Form as Shipped	⁷ Li ⁺	OH ⁻
Total Exchange Capacity	≥ 1.90 eq/L (H ⁺ form)	≥ 1.20 eq/L (OH ⁻ form)
Water Retention Capacity	49.0 – 55.0% (H ⁺ form)	54.0 – 60.0% (OH ⁻ form)
Ionic Conversion		
⁷ Li ⁺	≥ 99%	
OH ⁻		≥ 95%
CO ₃ ²⁻		≤ 5%
Cl ⁻		≤ 0.05%
SO ₄ ²⁻		≤ 0.1%
Particle Size		
Particle Diameter §	650 ± 50 μm	630 ± 50 μm
Uniformity Coefficient	≤ 1.20	≤ 1.10
< 300 μm	≤ 0.2%	≤ 0.2%
< 425 μm	≤ 5.0%	≤ 0.5%
> 1180 μm	≤ 2.0%	≤ 2.0%
Purity		
Metals, dry basis:		
Na	≤ 20 mg/kg	≤ 20 mg/kg
K	≤ 20 mg/kg	≤ 20 mg/kg
Fe	≤ 20 mg/kg	≤ 20 mg/kg
Cu	≤ 5 mg/kg	≤ 5 mg/kg
Co	≤ 5 mg/kg	≤ 5 mg/kg
Ca	≤ 10 mg/kg	≤ 10 mg/kg
Mg	≤ 10 mg/kg	≤ 10 mg/kg
Al	≤ 10 mg/kg	≤ 10 mg/kg
Hg	≤ 20 mg/kg	≤ 20 mg/kg
Heavy Metals (as Pb)	≤ 10 mg/kg	≤ 10 mg/kg
Other, dry basis:		
Cl		≤ 250 mg/kg
SiO ₂		≤ 10 mg/kg
Stability		
Whole Uncracked Beads	≥ 95%	≥ 95%
Friability:		
Average	≥ 400 g/bead	≥ 600 g/bead
> 200 g/bead	≥ 95%	≥ 95%
Solubility in Water	≤ 0.10%	≤ 0.10%
Density		
Shipping Weight	710 g/L (AMBERLITE™ IRN217 Li/OH)	

§ For additional particle size information, please refer to the [Particle Size Distribution Cross Reference Chart](#) (Form No. 177-01775).

Suggested Operating Conditions**

Temperature Range (Li ⁺ /OH ⁻ form) ‡	5 – 100°C (41 – 212°F)
pH Range (Stable)	0 – 14

‡ Operating mixed beds at elevated temperatures, for example above 60 – 70°C (140 – 158°F), may impact the purity of the loop and resin life. Contact our technical representative for details.


For additional information regarding recommended minimum bed depth, operating conditions, and regeneration conditions for [mixed beds](#) (Form No. 177-03705) or [separate beds](#) (Form No. 177-03729) in water treatment, please refer to our Tech Facts.

Hydraulic Characteristics

Estimated pressure drop for AMBERLITE™ IRN217 Li/OH Ion Exchange Resin as a function of service flowrate and temperature is shown in Figure 1. These pressure drop expectations are valid at the start of the service run with clean water.

Figure 1: Pressure Drop

Temperature = 10 – 60°C (50 – 140°F)



Product Stewardship

Dow has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our product stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our product stewardship program rests with each and every individual involved with Dow products—from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice

Dow strongly encourages its customers to review both their manufacturing processes and their applications of Dow products from the standpoint of human health and environmental quality to ensure that Dow products are not used in ways for which they are not intended or tested. Dow personnel are available to answer your questions and to provide reasonable technical support. Dow product literature, including safety data sheets, should be consulted prior to use of Dow products. Current safety data sheets are available from Dow.

For more information, contact our Customer Information Group:

Asia Pacific	+86 21 3851 4988
Europe, Middle East, Africa	+31 115 672626
Latin America	+55 11 5184 8722
North America	1-800-447-4369

www.dowwaterandprocess.com

WARNING: Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.

NOTICE: No freedom from infringement of any patent owned by Dow or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where Dow is represented. The claims made may not have been approved for use in all countries. Dow assumes no obligation or liability for the information in this document. References to "Dow" or the "Company" mean the Dow legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.

"All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. Nothing in this document should be treated as a warranty by Dow.

